


# Experience true individuality

## HEINE Binocular Loupes and Headlights. Ordering information.



### ML 4 LED HEADLIGHT WITH HR /HRP BINOCULAR LOUPES

#### TOPSELLER IN ALL SURGICAL SPECIALTIES



**ML 4 LED HeadLight Kits with HR or HRP Binocular Loupes**, with i-View loupe mount **and S-GUARD**, Headband Professional L, mPack and plug-in transformer, cleaning fluid, cleaning cloth

with HR Binocular Loupe 2.5x/340mm working distance	J-008.31.440
with HR Binocular Loupe 2.5x/420mm working distance	J-008.31.441
with HR Binocular Loupe 2.5x/520mm working distance	J-008.31.450
with HRP Binocular Loupe 3.5x/420mm working distance	J-008.31.442
with HRP Binocular Loupe 4x/340mm working distance	J-008.31.443
with HRP Binocular Loupe 6x/340mm working distance	J-008.31.444

**ML 4 LED HeadLight Kits with HR or HRP Binocular Loupes, without S-GUARD**, with i-View loupe mount, Headband Professional L, mPack and plug-in transformer

with HR Binocular Loupe 2.5x/340mm working distance	J-008.31.452
with HR Binocular Loupe 2.5x/420mm working distance	J-008.31.453
with HR Binocular Loupe 2.5x/520mm working distance	J-008.31.463
with HRP Binocular Loupe 3.5x/420mm working distance	J-008.31.454
with HRP Binocular Loupe 4x/340mm working distance	J-008.31.456
with HRP Binocular Loupe 6x/340mm working distance	J-008.31.457

**ML 4 LED HeadLight UNPLUGGED Kits with HR or HRP Binocular Loupes**, with i-View loupe mount **and S-GUARD**, Headband Professional L, Wall Transformer EN50 UNPLUGGED, 2 x mPack UNPLUGGED, cleaning fluid, cleaning cloth

with HR Binocular Loupe 2.5x/340mm working distance	J-008.31.445
with HR Binocular Loupe 2.5x/420mm working distance	J-008.31.446
with HR Binocular Loupe 2.5x/520mm working distance	J-008.31.451
with HRP Binocular Loupe 3.5x/420mm working distance	J-008.31.447
with HRP Binocular Loupe 4x/340mm working distance	J-008.31.448
with HRP Binocular Loupe 6x/340mm working distance	J-008.31.449

**ML 4 LED HeadLight UNPLUGGED Kits with HR or HRP Binocular Loupes, without S-GUARD**, with i-View loupe mount, Headband Professional L, Wall Transformer EN50 UNPLUGGED, 2 x mPack UNPLUGGED

with HR Binocular Loupe 2.5x/340mm working distance	J-008.31.458
with HR Binocular Loupe 2.5x/420mm working distance	J-008.31.459
with HR Binocular Loupe 2.5x/520mm working distance	J-008.31.464
with HRP Binocular Loupe 3.5x/420mm working distance	J-008.31.460
with HRP Binocular Loupe 4x/340mm working distance	J-008.31.461
with HRP Binocular Loupe 6x/340mm working distance	J-008.31.462



### LOUPELIGHT 2 WITH HR /HRP BINOCULAR LOUPES

#### MOST TRUSTED BY DENTISTS AND ENTS



**NEW! LoupeLight 2 Sets with HR/HRP Binocular Loupes** with i-View loupe mount on S-FRAME, detachable yellow filter, mPack mini, mPack mini Belt Clip, E4-USB plug-in transformer, protective lenses, 2 sterilisable levers, retaining cord, cleaning fluid, cleaning cloth, carrying case

with HR Binocular Loupe 2.5x/340mm working distance	C-008.32.450
with HR Binocular Loupe 2.5x/420mm working distance	C-008.32.451
with HR Binocular Loupe 2.5x/520mm working distance	C-008.32.452
with HRP Binocular Loupe 3.5x/420mm working distance	C-008.32.453
with HRP Binocular Loupe 4x/340mm working distance	C-008.32.454
with HRP Binocular Loupe 6x/340mm working distance	C-008.32.455




### HR /HRP BINOCULAR LOUPES

#### MOST TRUSTED BY DENTISTS AND ENTS



**Binocular Loupes Sets with i-View on S-FRAME**, Protective lenses, 2 sterilisable swivel levers, retaining cord, cleaning fluid, cleaning cloth, carrying case

with HR Binocular Loupe 2.5x/340mm working distance	C-000.32.355
with HR Binocular Loupe 2.5x/420mm working distance	C-000.32.356
with HR Binocular Loupe 2.5x/520mm working distance	C-000.32.567
with HRP Binocular Loupe 3.5x/420mm working distance	C-000.32.430
with HRP Binocular Loupe 4x/340mm working distance	C-000.32.431
with HRP Binocular Loupe 6x/340mm working distance	C-000.32.432



**Binocular Loupes Sets with i-View loupe mount and S-GUARD**, Headband Professional L, protective lenses, 2 sterilisable swivel levers, cleaning fluid, cleaning cloth

with HR Binocular Loupe 2.5x/340mm working distance	C-000.32.365
with HR Binocular Loupe 2.5x/420mm working distance	C-000.32.366
with HR Binocular Loupe 2.5x/520mm working distance	C-000.32.367
with HRP Binocular Loupe 3.5x/420mm working distance	C-000.32.440
with HRP Binocular Loupe 4x/340mm working distance	C-000.32.441
with HRP Binocular Loupe 6x/340mm working distance	C-000.32.442

**Binocular Loupes Sets without S-GUARD**, with i-View loupe mount, Headband Professional L, protective lenses, 2 sterilisable swivel levers

with HR Binocular Loupe 2.5x/340mm working distance	C-000.32.865
with HR Binocular Loupe 2.5x/420mm working distance	C-000.32.866
with HR Binocular Loupe 2.5x/520mm working distance	C-000.32.867
with HRP Binocular Loupe 3.5x/420mm working distance	C-000.32.840
with HRP Binocular Loupe 4x/340mm working distance	C-000.32.841
with HRP Binocular Loupe 6x/340mm working distance	C-000.32.842



### HEADLIGHTS

#### PERFECT ILLUMINATION




**NEW! MicroLight 2 Set on S-FRAME**, mPack mini, mPack mini Belt Clip, E4-USB plug-in transformer, retaining cord, cleaning fluid, cleaning cloth, carrying case

J-008.31.276

**NEW! MicroLight 2 Set on lightweight headband**, mPack mini, mPack mini Belt Clip, E4-USB plug-in transformer, carrying case

J-008.31.277



<b>ML 4 LED HeadLight on Headband Professional L</b> , without power source	J-008.31.410
<b>ML 4 LED HeadLight on Headband Professional L</b> , with plug-in transformer	J-008.31.411
<b>ML 4 LED HeadLight on Headband Professional L</b> , with mPack and plug-in transformer	J-008.31.413
<b>ML 4 LED HeadLight on Headband Professional L</b> , with mPack UNPLUGGED and plug-in transformer UNPLUGGED	J-008.31.415
<b>ML 4 LED HeadLight on Headband Professional L</b> , with wall mounted EN50 UNPLUGGED charger and 2x mPack UNPLUGGED	J-008.31.416



Distributed by  
**HENLEYS MEDICAL SUPPLIES LIMITED**  
Brownfields, Welwyn Garden City, Herts AL7 1AN  
Tel: 01707 333164 Fax: 01707 334795  
www.henleysmed.com

